

**ITEM # ATS22D62S6, SOFT START**

Soft Start



Specifications

<b>Family</b>	Altistart 22
<b>Product Line</b>	Soft Starters
<b>Application</b>	Constant & Variable Torque
<b>Enclosure Rating</b>	IP20 (IP00 if no connections)
<b>Frame Size</b>	B
<b>Output Ampere Rating</b>	63
<b>Maximum HP Rating 208V</b>	15
<b>Maximum HP Rating 230V</b>	20
<b>Maximum kW Rating 400V</b>	22
<b>Maximum HP Rating 460V</b>	40
<b>Maximum HP Rating 575V</b>	50
<b>Control Voltage</b>	220 Vac (-15% to + 10%)
<b>Logic Input</b>	3
<b>Analog Input</b>	1 PTC probe

<b>Analog Output</b>	N/A
<b>Logic/Relay Outputs</b>	2 (N/C / NO)
<b>Communication</b>	Modbus
<b>Weight [lb]</b>	17.20
<b>Weight [kg]</b>	7.80
<b>UL File No.</b>	E184727
<b>CSA File</b>	224330
<b>Other</b>	UL, CSA,CE,GOST,C-Tick,CCC and RoHS