



PRODUCT-DETAILS

BGM0505**STR BRASS FITTING M25 25MM-MET****General Information**

Extended Product Type:	BGM0505
Product ID:	7TCA297020R0058
EAN:	5011949200494
Catalog Description:	STR BRASS FITTING M25 25MM-MET
Long Description:	Fitting for Pliable Conduit, Straight with External Male Thread, Conduit Size 25mm, M25 Thread, Very High Mechanical and UV Protection, IP66, IP67 Ratings, Brass to BS2874 with Nylon Seals
Display Name:	BGM0505

Additional Information

Product Main Type:	KOPEX-EX FLEXIBLE CABLE PROTECTION
Application:	For Insertion Into Threaded Entries and Knockouts Using a Locknut to Secure

Ordering

EAN:	5011949200494
UPC:	786210284156

Technical

Number of Batteries:	0
Color:	Metallic
Material:	Brass with Nylon Seals
Size:	Conduit Size 25mm ; M25 Thread

Environmental

WEEE Category:	Product Not in WEEE Scope
----------------	---------------------------

RoHS Information: Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units:	10 piece
Package Level 1 EAN:	5011949200494
Package Level 1 Height:	7.48 in 190 mm
Package Level 1 Depth / Length:	11.41 in 290 mm
Package Level 1 Width:	12.99 in 330 mm

Certificates and Declarations

Declaration of Conformity - CE:	9AKK107492A9617
RoHS Declaration:	9AKK107992A8994
REACH Declaration:	9AKK107992A8994

External Classifications and Standards

ETIM 8:	EC001180 - Screw connection for protective metallic hose
ETIM 9:	EC001180 - Screw connection for protective metallic hose
UNSPSC:	39121311

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems