



## PRODUCT-DETAILS

**SPL16/M16/A****STR NPB FITTING M16 16MM-MET****General Information**

Extended Product Type	SPL16/M16/A
Product ID	7TCA296030R0091
EAN	5020963001024
Catalog Description	STR NPB FITTING M16 16MM-MET
Long Description	Nickel Plated Brass Liquid Tight Straight Fitting with Fixed External Threads, Nominal Conduit Size 16 Millimeters, Metric Thread Size M16

**Additional Information**

Product Main Type	Adaptaflex Flexible Cable Protection
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit

**Ordering**

EAN	5020963001024
UPC	786210245843

---

## Technical

Number of Batteries	0
Color	Metallic
Material	Brass
Size	3/8 Inch

---

## Environmental

WEEE Category	Product Not in WEEE Scope
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

---

## Container Information

Package Level 1 Units	10 piece
Package Level 1 EAN	5020963001024
Package Level 1 Height	9.84 in 250 mm
Package Level 1 Depth / Length	1 in 25 mm
Package Level 1 Width	7.87 in 200 mm

---

## Certificates and Declarations

Declaration of Conformity - CE	9AKK107492A9618
RoHS Declaration	9AKK107992A8994
REACH Declaration	9AKK107992A8994

---

## External Classifications and Standards

ETIM 8	EC001180 - Screw connection for protective metallic hose
ETIM 9	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121311

---

## Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

