

# AI-WM 1-8 RD - Ferrule




3240544

<https://www.phoenixcontact.com/gb/products/3240544>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Ferrule with insulating collar that can be labeled. When using the magazine, the ferrules can be labeled with BLUEMARK.



## Your advantages

- Electrogalvanized
- Ferrules made from electrolytic copper
- Highly resistant and optimum printing quality thanks to modern UV printing technology
- Crimping and marking in one step
- Ferrules can be labeled with BLUEMARK

## Commercial data


Item number	3240544
Packing unit	780 pc
Minimum order quantity	780 pc
Sales key	BH3415
Product key	BH3415
Catalog page	Page 201 (C-3-2019)
GTIN	4046356528146
Weight per piece (including packing)	0.248 g
Weight per piece (excluding packing)	0.245 g
Customs tariff number	85369010
Country of origin	DE

## Technical data

### Product properties

Product type	Cable end sleeve
--------------	------------------

### Dimensions

Dimensional drawing		
Width	4.6 mm	
Sleeve length	8 mm	
Ferrule diameter	1.8 mm	
Sleeve wall thickness	0.15 mm	
Inner dimensions of the insulating collar	3 mm	

### Internal dimensions

Internal diameter	1.5 mm
-------------------	--------

### Material specifications

Color	red (RAL 3001)
Material	E-CU
Flammability rating according to UL 94	HB
Coating	galvanically tin-plated
Surface characteristics	Tin-plated
Components	free from silicone and halogen

### Cable/line

External cable diameter	= 1.20 mm
-------------------------	-----------

### Mechanical properties

#### Technical data

Sleeve length	8 mm
---------------	------


### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Permanent temperature	105 °C (-40 °C no load / 0 °C dynamic load)
Short-term temperature	120 °C

## Drawings

Dimensional drawing



# AI-WM 1-8 RD - Ferrule

3240544

<https://www.phoenixcontact.com/gb/products/3240544>



## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/3240544>



**cULus Listed**

Approval ID: E488001

# AI-WM 1-8 RD - Ferrule



3240544  
<https://www.phoenixcontact.com/gb/products/3240544>

## Classifications

### ECLASS

ECLASS-13.0	27400201
-------------	----------

### ETIM

ETIM 9.0	EC000005
----------	----------

### UNSPSC

UNSPSC 21.0	27121700
-------------	----------

# AI-WM 1-8 RD - Ferrule

3240544

<https://www.phoenixcontact.com/gb/products/3240544>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)