



Multi Purpose Ergonomic Protection



Light Duty

Durable, comfortable industrial gloves with fully dipped nitrile coating, for 360° coverage

- **Heightened defenses:** HyFlex® 11-849 safety gloves' fully dipped design ensures 360° protection from light scratches and dirt
- **Improved durability:** Their FORTIX™ Abrasion Resistance nitrile foam coating guarantees EN abrasion resistance compliance
- **Enhanced grip:** HyFlex® 11-849 safety gloves come with 2x more grip, for better performance in dry or slightly oily conditions
- **Reduced contaminants:** HyFlex® 11-849 industrial working gloves are silicone-free, avoiding contaminant transfer to metal before painting
- **Certified harm-free:** Dermatest® and Oeko-Tex® certification ensure these PPE gloves are skin-friendly and free of harmful substances
- **Elevated comfort:** These HyFlex® gloves' Spandex® and nylon liner is shaped to natural hand contours



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Transportation
- Automotive Aftermarket

Applications

- Picking, fastening components
- Fastening components, parts
- Transport & Logistics
- General handling
- Occasional handling of hot objects : EN407 Contact Heat class 1 (100°C for 15s)
- Compatible with consumer and industrial touchscreens

Key Features

- Fully dipped coating: Industrial gloves with 360° hand protection
- FORTIX™ Abrasion Resistance: 2x more grip, up to 20% more durability
- Silicone-free: No contaminant transfer to metal prior to painting

Technologies



DMF free



Performance Standards & Regulatory Compliance



ANSI/ISEA 105-2024



EN388: 2016



4121A

EN 407



X1XXXX



STANDARD 100
1408033
Centexbel



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-849	Finishing: Fully Coated Coating Material: Foam Nitrile Liner Material: Spandex, Nylon Cuff Style: Knitwrist	18	6, 7, 8, 9, 10, 11	210-255 mm, 8.3-10 inches	Black	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699