



PRODUCT-DETAILS

BEH08**EX CONDUIT CLIP NC50 BLK****General Information**

Extended Product Type:	BEH08
Product ID:	7TCA297120R0418
EAN:	5011949240643
Catalog Description:	EX CONDUIT CLIP NC50 BLK
Long Description:	Conduit Clip, Conduit Size 50mm/NW48, Width 20mm, Height 65.0mm, IP68 Rating, Approved for Zones 1, 2, 21, 22, Modified Nylon 12 with Nickel Plated Threads, Black
Display Name:	BEH08

Additional Information

Product Main Type:	PMA Flexible Cable Protection
Application:	Supports Conduit to Rod, Wire or Flange
Product Type:	Clip for Securing Conduit Systems

Ordering

EAN:	5011949240643
------	---------------

Technical

Number of Batteries:	0
Color:	Black
Material:	Modified Nylon/Polyamide 12 with Nickel Plated Threads

Environmental

WEEE Category:	Product Not in WEEE Scope
----------------	---------------------------

Container Information

Package Level 1 Units:	10 EA
Package Level 1 EAN:	5011949240643
Package Level 1 Height:	302.26 mm 11.9 in
Package Level 1 Depth / Length:	210.82 mm 8.3 in
Package Level 1 Width:	401.32 mm 15.8 in

Certificates and Declarations

Data Sheet, Technical Information:	9AKK106930A7768
Instructions and Manuals:	BEH08
Declaration of Conformity - CE:	9AKK107680A0674

External Classifications and Standards

ETIM 8:	EC000464 - Fixing clamp
ETIM 9:	EC000464 - Fixing clamp
UNSPSC:	39121702

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems