

Datasheet

Stock No: 811-8257

RS Pro 3P+E DIN 43650 A Solenoid Connector



Product Details

DIN Connector Sockets, 2/3 Pole + Earth, Type A

A selection of 2 and 3 pole and earth, non-illuminated DIN connector sockets rated at 250Vac. These screw mount sockets are Type A, available with PG9 and PG11 glands and are of Nylon-6 GF construction, with a Nitrile/silicon gasket.

Features and Benefits:

- 2 and 3 Pole + earth versions
- Type A socket Type
- Gland size PG-9 and PG-11 variants
- Contact resistance 20mΩ max.
- Permissible Temperature 0 to 90° C
- HV breakdown test 2KV AC for 1 minute

RS DIN 43650 Solenoid Components



ENGLISH

Specifications

Pole Format	3P+E
DIN 43650 Type	DIN 43650 A
Voltage Rating	250 V ac
Gender	Female
Mounting Type	Cable Mount
Cable Gland Size	PG11
Colour	Black
Current Rating	10A
Series	ME-309/S
Termination Method	Screw