



ENGLISH

RS Pro Polyether PUR 10m Long transparent Flexible Ducting Reinforced, 50mm Bend Radius , Applications Various

RS Stock No. 362-2035

Brand RS Pro



Image representative of range

Product Details

Non-toxic Flexible Ducting

RS Pro polyurethane (PU) polyether hose with a PVC spiral. Can be used for suction, the transport of abrasive materials and dry foods.

White PVC helix in a clear non-toxic polyether polyurethane

Convolute cover

High abrasion resistance

Also suitable for wet applications such as pharmaceutical preparation, fish transfer or leaf and grass collection

Temperature range -25 to +85°C

Note

All data refers to performance at 18°C. Any changes in temperature will affect the performance data



Polyurethane Ducting - Lightweight

Specifications

Not what you're looking for? Select the attributes you require, then click the button below

<input type="checkbox"/>	Inner Diameter	50mm
<input type="checkbox"/>	Outer Diameter	57.4mm
<input type="checkbox"/>	Material	Polyether PUR
<input type="checkbox"/>	Length	10m
<input type="checkbox"/>	Suitable Applications	Abrasive Material, Agriculture, Cereal, Gardening, Grain, Organic Material, Powder, Scrap Processing, Suction
<input type="checkbox"/>	Colour	Transparent
<input type="checkbox"/>	Bend Radius	50mm
<input type="checkbox"/>	Reinforced	Yes