

Technical data sheet

Article number:
924-00499

CE1

Product Group	Closed End Connectors
Product Family	Bootlace Terminals
Material	Aluminium (AL), Polyamide 6.6 (PA66)
Colour	Transparent (CL)
Application Range	Low Voltage
Conductor Size Range mm ²	0.50-1.5 mm ²
Diameter (D)	6.2 mm
Length (L)	17.9 mm
Length (L2)	11.5 mm
Max Voltage	600 V
Operating Temperature	+105 °C
Package Content	50 pcs.
Package Content packed in	bag
REACH Reg. Art.33 does not contain SVHC	Yes
ROHS compliant	Yes
Width (W)	4.6 mm

