



SDS-Plus MX4 NG Set 3 - 10 pc

SDS-PLUS MX4 DRILL BITS - 4 CUT

- The Milwaukee MX4™ SDS-Plus drill bit is engineered for the toughest applications, featuring innovative fully welded solid carbide tip technology (up to $\varnothing$ 20 mm) for maximum durability in rebar and unmatched drilling speed in concrete.
- 4-Cutter solid carbide tip: Enhanced geometry with a sharp centering tip, rebar guards, and new dust grooves delivers clean starts, precise holes, and maximum life when drilling through rebar - even under extreme jobsite conditions.
- Optimised flute design with reinforced core: A thicker core combined with alternating SPEED and HEAVY-DUTY spirals ensures fast debris removal, reduced friction, and superior stability in demanding applications.
- Convex shank for maximum energy transfer: The convex shank end optimises energy transfer from tool to tip, boosting impact force, drilling efficiency, and jobsite productivity.
- One-Piece slotted carbide tip for $\varnothing > 20$ mm: For large-diameter concrete drilling, this design offers exceptional strength, extended bit life, and break resistance in heavy-duty use.
- PGM certified: Meets industry standards for precision and safety, making it the ideal choice for anchor setting.
- Made in Germany: Manufactured to the highest standards for uncompromising quality, reliability, and performance on every jobsite.
- Made in Germany.



Article Number	4932500062
Contents	$\varnothing$ 5 / 6 / 6 x 115 mm, $\varnothing$ 6 / 6 / 8 / 8 / 8 / 10 / 12 x 165 mm
Pack quantity	10