

Product data sheet

Specifications



Spacial SM compact enclosure with mounting plate - 2000x1000x500 mm

NSYSM2010502DP

Main

Range	Spacial
Product name	Spacial SM
Product or component type	Compact enclosure
Application	Multi-purpose
Installation accessory type	Floor-standing
Device composition	1 body 2 door 1 cable gland plate 1 locking system with handle: door 1 blocking system: left door 4 mounting plate bracket 1 mounting plate
Removable parts	Door by screws hinge Mounting plate by screws mounting plate bracket Mounting plate bracket by screws
Enclosure nominal height	2000 mm
Enclosure nominal width	1000 mm
Enclosure nominal depth	500 mm

Complementary

Number of doors	Front: 2 door(s)
Door opening side	Left (120 °) Right (120 °)
Door type	Plain
Lock type	4 points lock, handle with 5 mm double bar insert
Body type	Front part forming a rigid frame with welded corners Single piece body with welded rear panel
Mounting plate description	Plain
Type of gland plate	Standard
Cable entry	1 entry
Material	Mounting plate: galvanised steel Body: sheet steel Door: sheet steel Hinge: zamak
Surface finish	Epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035) Handle: black (RAL 9005)

Accessibility for operation	Front
Net weight	165 kg

Environment

Standards	IEC 62208
Product certifications	DNV BV UL
IK degree of protection	IK10 conforming to IEC 62262
IP degree of protection	IP55 conforming to IEC 60529

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	165.0 kg
Package 1 Height	213.0 cm
Package 1 width	104.5 cm
Package 1 Length	59.0 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------