



Sample photo

Order symbol: ABS 200/63 HT
Product nbr: 6081924
Description: Enclosure, ABS
Remarks: Smoked transparent cover

EAN: 6418074052001
El. number:
Finland: 3435278
Denmark: 8212023686
Sweden: 2535869
Norway:

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height
mm:	255	180	63
inch:	10.0	7.1	2.5

Materials:

Material: ABS
Base colour: RAL 7035
Cover colour: Smoked grey
Cover screws material: Polyamide
Cover screws colour: Black
Gasket material: TPE

Temperatures:

Short term: -40 ... 80 °C
Continuous: -40 ... 60 °C
Short term: -40 ... 175 °F
Continuous: -40 ... 140 °F

Accessories:

MIV 200 Mounting plate (Galvanized steel)
MIN 15 DIN-15 Mounting rail
MIN 20 DIN-15 Mounting rail
MIV 15 DIN-35 Mounting rail
MIV 20 DIN-35 Mounting rail
FP A 200/180 Front plate (Aluminium)
HFP 180 Front plate hinge series (2 pcs)
FP 22046 Wall fastening lug (4 pcs)

Rating:

Ingress Protection (EN 60529): IP 66/67
Impact Resistance (EN 62262): IK 07
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): Yes
Flammability Rating (UL 746 C 5): UL 94 HB
Glow Wire Test (IEC 695-2-1) °C: 650
NEMA Class: NEMA 1, 4, 4X, 6, 12, 13

Certificates:

Fimko
Europe EN 62208: 2003
Gost R

