

Features

- *Conductor*
Material: tinsel wires
- *Jacket Material:*
PVC, black
- *Cable Length:* 3M
- *Easy to install and reliable connection*
- *Color:* Black

RS PRO Telephone Cable

RS Stock No.: 0707872



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against

demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

This is a coiled RJ12 6P6C to RJ12 6P6C data cable for both data and voice use, coiled length is 520mm, extended length is 3M. It is good for long-distance communication for your desk phone or office phone. Extended length coiled cord is provided extra length for working in the office or at home. Both ends are durable RJ12 6P6C modular connector.

Straight-through pin out for both data and voice use.

It can be used as a regular telephone cord, fax cable, DSL modem cable, cash drawer cable and also in printer system, radio system, control system etc.

General Specifications

<i>Number of Strands</i>	<i>6</i>
<i>Conductor Strand Type</i>	<i>Stranded</i>
<i>Terminated/Unterminated</i>	<i>Terminated; Unterminated</i>
<i>Connector Type</i>	<i>Male RJ12/RJ12</i>
<i>Connector B</i>	<i>Male RJ12</i>
<i>Connector A</i>	<i>Male RJ12</i>
<i>Outer Sheath Material</i>	<i>PVC;</i>
<i>Sheath Colour</i>	<i>Black</i>
<i>Conductor Material</i>	<i>Tinsel Copper wire</i>
<i>Drain Wire</i>	<i>No</i>
<i>Fire Behaviour</i>	<i>Flame Retardant.</i>

Mechanical Specifications

<i>Length</i>	<i>3m</i>
<i>Outer Diameter</i>	<i>6.5*2.4mm</i>
<i>Sheath Thickness</i>	<i>0.6mm</i>

<i>Insulator Diameter</i>	0.9mm +/-0.05
<i>American Wire Gauge</i>	28AWG
<i>Cross Sectional Area</i>	0.079mm ²
<i>Size of Strands</i>	7/0.12mm, 28AWG
<i>Core Strands</i>	7/0.12mm

Approvals

<i>Compliance/Certifications</i>	RoHS, Reach
<i>Declarations</i>	RoHS, Reach

