

Previously known as: Sensilite



Multi Purpose



Light Duty

Dexterous, durable light-duty work gloves, ensuring superb comfort for intricate handling

- **Elevated comfort:** HyFlex® 48-102 industrial gloves are designed with fine, stretchable stitches, granting wearers outstanding comfort
- **Augmented dexterity:** These light-duty gloves also feature a thin liner and coating design, delivering heightened levels of dexterity and flexibility and facilitating more intricate handling
- **Improved durability:** Their robust palm-dipped polyurethane coating results in highly abrasion-resistance gloves that satisfy EN level 4 abrasion resistance standards
- **Reduced replacement costs:** Low-linting by design, these safety gloves boast a longer wear life, making for fewer glove replacements and related costs over time



Industries

- Automotive
- Automotive Aftermarket
- Electronics
- Machinery and Equipment
- Warehousing
- Logistics
- Transportation

Applications

- Machine tool operation
- Finishing works
- General handling
- Packaging

Previously known as: Sensilite

Key Features

- **Fine, stretchable stitches:** Excellent everyday comfort
- **Thin liner and coating design:** Superb dexterity and flexibility
- **Polyurethane palm coating:** Heightened abrasion resistance

Vulcanization Chemical Accelerators

- Natural rubber proteins (in knitwrist elastic)

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance



EN388: 2016



4121A

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 48-102	Finishing: Palm Coated Coating Material: Polyurethane Liner Material: Nylon Cuff Style: Knitwrist	13	6, 7, 8, 9, 10, 11	219-270 mm	Grey	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.