



Version Information	
Product Name	Microsoft® Comfort Mouse 3000
Product Version	Microsoft Comfort Mouse 3000
Mouse Version	Microsoft Comfort Mouse 3000
Product Dimensions	
Mouse Length	4.53 inches (115 millimeters)
Mouse Width	2.58 inches (65.6 millimeters)
Mouse Depth/Height	1.61 inches (40.8 millimeters)
Mouse Cable Length	78.7 inches (2000 millimeters)
Mouse Weight	0.20 ounces (92 grams)
Compatibility and Localization	
Interface	USB compatible
Operating Systems <sup>1</sup>	<ul style="list-style-type: none"> <li>• Microsoft Windows® 8.1, Windows 8, Windows RT 8.1, Windows RT 8, and Windows 7</li> <li>• Macintosh Mac OS X v10.7-10.9</li> <li>• Android 3.2 and 4.2</li> </ul> <p><sup>1</sup>Advanced functionality not available with all devices and/or operating systems. See compatibility information at: <a href="http://www.microsoft.com/hardware/compatibility">www.microsoft.com/hardware/compatibility</a></p>
Top-line System Requirements	<p>Requires a PC that meets the requirements for and has installed one of these operating systems:</p> <ul style="list-style-type: none"> <li>• Windows 8.1, Windows 8, or Windows 7</li> <li>• 100 MB</li> <li>• USB port</li> </ul> <p>You must accept License Terms for software download at: <a href="http://Microsoft.com/hardware/downloads">Microsoft.com/hardware/downloads</a>. Broadband required. Added charges may apply.</p>
Compatibility Logos	<ul style="list-style-type: none"> <li>• Compatible with Microsoft Windows 8 and Windows RT</li> <li>• Mac logo</li> </ul>
Software Localization	Microsoft Mouse and Keyboard Center software may be installed in Simplified Chinese, Traditional Chinese, English, French, German, Italian, Japanese, Korean, Brazilian Portuguese, Iberian Portuguese, or Spanish. If available, standard setup will install the software in the default OS language. Otherwise, the English language version will be installed.
Tracking Technology	
Mouse Tracking System	Microsoft-proprietary BlueTrack™ Technology
Imaging Rate	Dynamically adaptable to 8000 frames per second
X-Y Resolution	1000 points per inch (39.4 points per millimeter)
Tracking Speed	Up to 72 inches (1829 millimeters) per second
Acceleration	Up to 28G max
Product Feature Performance	
Mouse Button Features	3 customizable buttons
Right & Left Button Life	3,000,000 actuations at no more than 4 actuations per second
Wheel Button Life	150,000 actuations at no more than 4 actuations per second
Mouse Scrolling Features	Standard vertical scrolling
Wheel Vertical Scrolling Life	<ul style="list-style-type: none"> <li>• 100,000 revolutions (away from user) at no more than 60 rotations per minute</li> <li>• 300,000 revolutions (toward user) at no more than 60 rotations per minute</li> </ul>
Storage Temperature & Humidity	-40 °F (-40 °C) to 140 °F (60 °C) at <5% to 65% relative humidity (non-condensing)
Operating Temperature & Humidity	32 °F (0 °C) to 104 °F (40 °C) at <5% to 80% relative humidity (non-condensing)
Certification Information	
Country of Manufacture	People's Republic of China (PRC)
ISO 9001 Qualified Manufacturer	Yes
ISO 14001 Qualified Manufacturer	Yes
Restriction on Hazardous Substances	This device complies with all applicable worldwide regulations and restrictions including, but not limited to: EU directive 2002/95/EC on the Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment and EU Registration Evaluation and Authorization of Chemicals (REACH) regulation regarding Substances of Very High Concern.
FCC ID	This device complies with Part 15 of the FCC Rules and Industry Canada ICES-003. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Tested to comply with FCC standards. For home and office use. Model number: 1479, Comfort Mouse 3000.
Agency and Regulatory Marks	<ul style="list-style-type: none"> <li>• ACMA Declaration of Conformity (Australia and New Zealand)</li> <li>• ICES-003 report on file (Canada)</li> <li>• EIP Pollution Control Mark, EPUP (China)</li> <li>• CE Declaration of Conformity (European Union)</li> <li>• WEEE (European Union)</li> <li>• VCCI Certificate (Japan)</li> <li>• KCC Certificate (Korea)</li> <li>• GOST Certificate (Russia)</li> <li>• CITC Letter (Kingdom of Saudi Arabia)</li> <li>• BSMI Certificate (Taiwan)</li> <li>• FCC Declaration of Conformity (USA)</li> <li>• UL and cUL Listed Accessory (USA and Canada)</li> <li>• CB Scheme Certificate (International)</li> </ul>
Windows Certification Kit (WCK)	ID: 1608565 (32-bit) and 1608587 (64-bit) Microsoft Windows 8.1