

Main

Range of product	Mureva Styl
Product or component type	Timer
Device presentation	Complete product
Colour tint	White (RAL 9003)




Complementary

Device mounting	Surface
Technology type	Electromechanical
[Us] rated supply voltage	230 V AC 50/60 Hz
Load interrupting current	10 A resistive cos phi = 1 6 A inductive cos phi = 0.6
Time delay	2 minutes 2...14 minutes
Rated current	10 A
Control type	Turn button
Condition of use	Indoor/outdoor
Material	SEBS PP (polypropylene) ABS (acrylonitrile butadiene-styrene)
Fixing mode	By screws
Cable entry	Easy valve access diameter: 6...20 mm
Height	80 mm
Width	80 mm
Depth	76 mm
Chemical and detergent products resistance	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Quality labels	EAC CE
IP degree of protection	IP55
IK degree of protection	IK08
Flame retardance	Self-extinguishing 650 °C conforming to IEC 60695-2-1
Standards	EN 60669-2-1
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-25...55 °C

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration