

## **A-10 ; 0...16 bar gauge; 0 ... 10 V, 3-wire @ 14...30 V DC**

### **Pressure transmitter Model A-10**

Item number: 12784720

Quantity: 1 pcs.

Order code: A-10-6-BG416-HD1Z-FC-AGZ-ZW W1011A10Z-SZ3S-ZZFWPA-3AZZZSAZZZA3Z

Overview: A-10 ; 0...16 bar gauge; 0 ... 10 V, 3-wire @ 14...30 V DC  
Pressure transmitter Model A-10  
Non-linearity: 0.5% BFSL  
Process connection: G 1/4 A DIN EN ISO 1179-2; Sealing: NBR  
Electrical connection: valve connector, size A  
Pin assignment: U+=1, U-=2, S+=3  
Permissible medium temperature: 0...+80 °C  
Approvals: cULus  
Type of packaging: folding box single  
WIKA standard - specification according to data sheet PE 81.60

Details: Pressure transmitter Model A-10  
for general applications  
Specifications according to data sheet: PE 81.60  
Wetted parts: 316L  
Case: 316L  
Non-linearity: 0.5% BFSL  
Unit: bar  
Pressure type: gauge  
Measuring range: 0...16 bar gauge  
Process connection: G 1/4 A DIN EN ISO 1179-2  
Sealing: NBR  
Permissible medium temperature: 0...+80 °C  
Output signal: 0 ... 10 V, 3-wire  
Power supply: 14...30 V DC  
Electrical connection: valve connector, size A  
Approvals: cULus  
W1 (Wika standard)  
Customer address: [www.wika.com](http://www.wika.com)  
Model name customer-specific: A-10  
Pressure port: Standard  
Type of packaging: folding box single  
Sealing colour: WIKA standard (blue)  
Test protocol: with test protocol  
Main Language: English  
Pin assignment: U+=1, U-=2, S+=3  
Customer-specific: WIKA standard - specification according to data sheet  
Model: A-10 2.0

Date: 23/01/2024



Operating Instructions: with printed OI  
Additional Data: without