



6311DDU

Single-Row Deep Groove Ball Bearings

Boundary Dimensions

d	55	mm	Bore diameter
D	120	mm	Outside diameter
B	29	mm	Width
r (min.)	2	mm	Chamfer dimension

Basic Load Ratings

Cr	78500	N	Basic dynamic load rating
C0r	44500	N	Basic static load rating

Speeds

Grease	4000	min-1	Grease lubrication
--------	------	-------	--------------------

Abutment and Fillet Dimensions

da (min.)	64	mm	Diameter of shaft abutment
da (max.)	72.5	mm	Diameter of shaft abutment
Da (max.)	111	mm	Diameter of housing abutment
ra (max.)	2	mm	Radius of shaft or housing fillet

Calculation factors

fo	13.1		Factor
----	------	--	--------

Additional information

z	8		Number of Balls
Dw	20.638	mm	Ball Diameter

Mass

Mass approx.	1.37	kg	Mass approx.
--------------	------	----	--------------

