

CIRCLIP PLIER INNER STRAIGHT PRO 225MM



- Invisible return spring for easier operation
- For use with inner type circlips or snap rings
- Bearing steel tips for heavy duty applications
- Non slip tip angle enabling the ring to stock securely to the tip when compressing or expanding the circlip
- Chrome vanadium construction
- Vinyl grip for easier use in pockets or tool pouches
- DIN 5256

9" Straight/Inner Circlip Plier Vinyl Grip with Spring

General information

Country of origin: Taiwan
Barcode: 5020385072039
Tariff code Europe: 8203200000
ECCN US: EAR99
ETIM: EC002228
UNSPSC: 27112110

Dimensions

Net weight (g): 295
Length: 235 mm
Length 2: 9"

Attributes

Product type: Circlip Pliers
Material: CrV, Bearing Steel
Certificates: N/A
Size: 2.3 mm
Capacity (mm): 40-100
Handle type: Vinyl
Return spring: Yes
Tip or blade type: Straight, Inner

Features



Technical changes and errors may occur. 01-08-2024 19:50



DESIGNED IN SWEDEN

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



Sandbergsvägen 3
 441 39 Alingsås, Sweden