


## Technical data

AS1115

Thrust washer



### VISUAL (S)



### PRODUCT DEFINITION

|                                          |          |
|------------------------------------------|----------|
| Brand                                    | NTN      |
| Dp - External diameter AS support washer | 100 mm   |
| Dp1 - Bore diameter AS support washer    | 75 mm    |
| S - Support washer thickness AS          | 1 mm     |
| Bearing ring (washer) AS mass            | 0,027 kg |

### PRODUCT PERFORMANCE

|                                  |           |
|----------------------------------|-----------|
| Tmin - Min operating temperature | 253,15 °K |
| Tmax - Max operating temperature | 393,15 °K |



**NTN Europe**

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15