



注  
△ 海外向製品

| 型番       | 嵌合相手型番   | 仕上     | $\phi D$ | $L1$ | $L2$ | 通用工具型番    | 製品規格番号   | 分類       |
|----------|----------|--------|----------|------|------|-----------|----------|----------|
| 170020-1 | 170021-1 | 電気錫めっき | 3.5      | 17.0 | 7.3  | 2088544-1 | 108-5004 | $\phi 4$ |
| 170020-2 | 170021-2 | 電気錫めっき | 4.0      | 18.0 | 8.7  | 2088544-1 | 108-5003 | $\phi 5$ |
| 170020-3 | 170021-3 | —      | 4.0      | 18.0 | 8.7  | 2088544-1 | 108-5003 | $\phi 5$ |
| 170020-4 | —        | —      | 3.5      | 17.0 | 7.3  | 2088544-1 | 108-5004 | $\phi 4$ |

単位: 耗 DIMENSIONS IN MM DO NOT SCALE PRINT

|     |                   |      |                 |
|-----|-------------------|------|-----------------|
| DR  | Y. Tanaka 1/22/14 | DE   |                 |
| CHK | T. Suguki 1/22/14 | APP. | y. Sato 1/21/14 |

|   |                      |   |   |   |     |
|---|----------------------|---|---|---|-----|
| ©1974 日本エー・エム・ピー株式会社<br>AMP社の諸製品は特許又は特許出願中                          |                      | ©1974 BY AMP (Japan), Ltd. ALL RIGHTS RESERVED AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING |   | 参考図面<br>(CUSTOMER COPY)<br>(REFERENCE ONLY) |     |
| 材料 (MATERIAL)<br>黄銅 板厚 0.5  |                      |   | Tyco Electronics<br>Tyco Electronics Corporation<br>Kawasaki, Japan |   |     |
| 仕上 (FINISH)<br>表参照  |                      |   | 分類 (CLASS)<br>表参照   |   |     |
| 包合電線断面積 (WIRE RANGE)<br>0.50 ~ 2.27 mm <sup>2</sup> (AWG #20 ~ #14) |                      |   | 型式 (TYPE)<br>—  |   |     |
| 被覆外径 (INSULATION DIA)<br>2.2 ~ 3.1 mm (— IN)                        |                      |   | 一般公差 (TOLERANCE EXCEPT AS NOTED) ±0.4 ±1°                           |   |     |
| LTR   | 変更 (REVISION RECORD) | DR.   | CHK.  | DATE  | REV |
| 4-1   | J A4                 | C-170020  | A   |   |     |
| 名称 (NAME) $\phi 4$ 及び $\phi 5$ シュア プラグ (shur plug)                  |                      |   |   |   |     |