

TRANSPARENT FRONT PLATE W600/W650 4M

LVS03342

EAN Code: 3606481873729

Main

Range	PrismaSeT	
Range of product	PrismaSeT G PrismaSeT P	
Product or component type	Front plate	
Accessory / separate part category	Installation accessory	
Range compatibility	PrismaSeT PrismaSeT G enclosure PrismaSeT PrismaSeT P cubicle	
Type of front plate	Transparent	
Installed device	TeSys: fixed TeSys U - horizontal installation TeSys: fixed GV2 + D or K contactors <= 40 A - horizontal installation PowerLogic: iEM3000 PowerLogic: PM3000	
Poles description	9 x 3P: modular rail support: TeSys U horizontal installation 9 x 3P: modular rail support: GV2 + D or K contactors <= 40 A horizontal installation	
Operating position	Horizontal	

Complementary

_		
Enclosure/cubicle description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm depth 400 mm Pack enclosure - width 555 mm	
Connection position	Direct connection	
Number of vertical modules [50 mm]	4	
Standards	IEC 61439-2 IEC 61439-1	
Product certifications	ASTA	
Material	Glass	
Surface finish	Textured Matt	
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder	
Colour	White (RAL 9003)	
Height	200 mm	
Width	500 mm	
Net weight	0.98 kg	
Quantity per set	Set of 1	

functional unit 600 mm PrismaSeT G floor-standing enclosure TeSys GV2 + D or K contactors <= 40 A fixed horizontal 3P 9 direct 5 600 mm PrismaSeT G wall-mounted enclosure TeSys GV2 + D or K contactors <= 40 A fixed horizontal 3P 9 direct 5 650 mm 400 mm PrismaSeT P cubicle TeSys GV2 + D or K contactors <= 40 A fixed horizontal 3P 9 direct 5 650 mm 400 mm PrismaSeT P cubicle PowerLogic 3 4 650 mm 400 mm PrismaSeT P cubicle PowerLogic 4 4 $600~\mathrm{mm}$ PrismaSeT G floor-standing enclosure TeSys TeSys U fixed horizontal 3P 9 600 mm PrismaSeT G wall-mounted enclosure TeSys TeSys U fixed horizontal 3P 9 direct 5 600 mm PrismaSeT G floor-standing enclosure TeSys TeSys U fixed horizontal 3P 9 direct 4 600 mm PrismaSeT G wall-mounted enclosure TeSys TeSys U fixed horizontal 3P 9 direct 4

650 mm 400 mm PrismaSeT P cubicle TeSys TeSys U fixed horizontal 3P 9 direct 4

Packing Units

_	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	21.5 cm
Package 1 Length	51.5 cm
Package 1 Weight	1.058 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	16 cm
Package 2 Width	23 cm
Package 2 Length	53 cm
Package 2 Weight	8.672 kg
Unit Type of Package 3	P12
Number of Units in Package 3	64
Package 3 Height	36 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	81 kg

Logistical informations

Country of origin FR

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability

Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better


Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
Halogen content performance	Halogen free plastic parts product
PVC free	Yes

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions



- All dimensions are approximate and are in
 Also see technical documentation.