

894 32

Single open ended spanner

metric

Code	ETIM
6576540	EC002130
EAN	UNSPSC
4010886657652	27-11-17-06
Country of origin	eCl@ss
India	21-04-01-01
Customs tariff number	
82041100	



Article description

- Acc. to DIN 894, ISO 3318
- Manganese phosphate finish up to 38 mm, steel-grey up from 41 mm
- Size 10 - 135 mm with angling hole
- Carefully forged and professionally machined:
- Jaw: ground precisely to exact nominal size for optimum contact areas
- Jaw set at 15°
- Secure grip thanks to profile shaft - very ergonomic and handy
- Overloading indicated by deformation
- * not standardised

Article information

Contents (Qty of pieces)	1	Standard	DIN 894 ISO 3318
Net weight [kg]	0,374 kg	Width across flats l [mm]	32
Total length [mm]	272 mm	Head height l [mm]	11,8 mm
Total width [mm]	63 mm	Width of head l [mm]	66,0 mm
Total height [mm]	12 mm	Jaw set	15 °
Surface	manganese phosphated	Ratchet function	no
Material	Vanadium steel 31CrV3		