

# S400



Steckschlüssel-Satz 1/2".

DIN 3120 / ISO 1174

Ausführung: Matt verchromt.

Werkstoff: CHROM-VANADIUM.

Kunststoff-Koffer: Öl- und temperaturbeständiges Polypropylen, 430 x 330 x 90 mm.

Inhalt: 40 Teile.

21 1/2" 6-kant Einsätze 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 25, 26, 27, 28, 30, 32 mm.

2 1/2" Verlängerungen, 125 und 250 mm.

1 1/2" Kardangelen.

1 1/2" T-Gleit-Adapter.

1 1/2" Gelenkgriff, 250 mm.

1 1/2" Umschaltknarre, 54 Zähne.

13 Ringmaulschlüssel 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19 mm.

Mit Dynamic-Drive Profil.



731415+



mm



S400

0111053

1

430x330x90

7225