



Save as PDF



9440 Remote Area Lighting System



The most innovative RALS unit to date, the 9440 moves fast to light up ravines, confined spaces, riverbanks... anyplace generator lights can't go. Deployed, the mast extends 7 feet high, shining light over low obstructions encountered by traditional lantern style lights. With a 120 degree beam spread and up to 2400 lumens, the entire emergency area will have the light you need for a safe and swift operation.

The 9440 is maintenance free, using super tough LED lamp modules and NiMH batteries for up to 6 hours of continuous light.



Black Yellow

Light Source

LED Type	LED Life	Tested Lumen Value
LED	50000	1200 (Low) 2400 (High)
Lamp Heads	Number of LEDs	Beam Spread
1	10	120
Brightness Settings	IP Rating (Ingress Protection)	
2		

Power Source

Battery Type	Battery Burn Time	Battery Charging Time	Battery Life
NiMH	6 (Low) 3 (High)	8 hrs.	300
Low Battery Warning	12V Primary Sockets	12V Auxiliary Sockets	
level indicator	1	0	
Watts	Voltage		
	9.6		

Dimensions & Weight

Head Length	Head Width	Head Depth
20cm.	20cm.	8.9cm.
Width Closed	Length Closed	Height Closed
20cm.	95cm.	0cm.
Mast Height Extended	Cord Length	Weight
0 cm.	0cm.	7.3kg.

Materials

Head	Body	Mast
Polycarbonate/ABS	Polycarbonate/ABS	Aluminium
Lens	Switch Type	
Polycarbonate	Silicone rubber keypad	

Configuration

Cat. #	Description
9440	9440 Remote Area Lighting System

9440 Remote Area Lighting System Accessories

No accessories are currently available for this product

Approvals

RoHS (Restriction of Hazardous Substances)
Compliant