

**SOLID PC 3828 13 T**



Sample photo

**Order symbol:** PC 3828 13 T  
**Product nbr:** 5330063  
**Description:** Enclosure, PC  
**Remarks:** Transparent cover

**EAN:** 6418074005557  
**El. number:**  
 Finland: 3423817  
 Italy: 7402050  
 Sweden: 2539452

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

| Dimensions:                   |  | Length               | Width | Height | Rating:                                     |
|-------------------------------|--|----------------------|-------|--------|---|
| <b>mm:</b>                    |  | 378                  | 278   | 130    | Ingress Protection (EN 60529): IP 66/67     |
| <b>inch:</b>                  |  | 14.9                 | 10.9  | 5.1    | Impact Resistance (EN 62262): IK 08/09      |
| <b>Materials:</b>             |  |                      |       |        | Electrical insulation: Totally insulated    |
| <b>Material:</b>              |  | Polycarbonate        |       |        | Halogen free (DIN/VDE 0472, Part 815): Yes  |
| <b>Base colour:</b>           |  | RAL 7035             |       |        | UV resistance: UL 508                       |
| <b>Cover colour:</b>          |  | Clear transparent    |       |        | Flammability Rating (UL 746 C 5): UL 94 5V  |
| <b>Cover screws material:</b> |  | Polyamide            |       |        | Glow Wire Test (IEC 695-2-1) °C: 960        |
| <b>Cover screws colour:</b>   |  | Grey                 |       |        | NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12 |
| <b>Gasket material:</b>       |  | Polyurethane         |       |        |   |
| <b>Temperatures:</b>          |  |                      |       |        | <b>Certificates:</b>                        |
| <b>Short term:</b>            |  | -40 ... 120 °C       |       |        | Underwriters Laboratories                   |
| <b>Continuous:</b>            |  | -40 ... 80 °C        |       |        | Fimko                                       |
| <b>Short term:</b>            |  | -40 ... 250 °F       |       |        | Europe EN 62208: 2003                       |
| <b>Continuous:</b>            |  | -40 ... 175 °F       |       |        | UL Canada                                   |
| <b>Accessories:</b>           |  |                      |       |        | Gost R                                      |
| EKPVT                         |  | Mounting plate       |       |        |   |
| EKV 22                        |  | DIN-35 Mounting rail |       |        |   |
| EKV 32                        |  | DIN-35 Mounting rail |       |        |   |
| EKPZR                         |  | Extension frame      |       |        |   |

