



Part Number : [1300230004](#)

Product Description : Super-Safeway Single Button, 3 Pin, Single-Pole, Single-Throw, Normally Open, 10A, Snap Action Switch, Nitrile/PVC Switch Boot, 125/250V AC, Mini-Change Connection

Series Number : 130128

Status : Active

Product Category : Push Button Products

Engineering Number : 55504

Documents & Resources

Drawings

[1300230004_sd.pdf](#)

Specifications

[1300230001_APPSPEC-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Push Button Products
Series	130128
Description	Super-Safeway Single Button, 3 Pin, Single-Pole, Single-Throw, Normally Open, 10A, Snap Action Switch, Nitrile/PVC Switch Boot, 125/250V AC, Mini-Change Connection
Enclosure Rating	Weather Resistant
Product Name	Super-Safeway
Type	Enabling Switch, PushButton Pendant Station
UPC	78678855509

Agency

UL	E70531
----	--------

Electrical

Voltage - Maximum	125V AC / 250V AC
-------------------	-------------------

Physical

Cord Diameter	N/A
Cord Grip Body Size	N/A
Cord Length	N/A
Cord Type	N/A
Emergency Stop	No
Material - Body	Nylon

Net Weight	70.760/g
Number of Speeds	Single
Packaging Type	Carton
Poles	1

This document was generated on Nov 05, 2025