



tesa® 4308

Product Information



Masking tape for high demanding applications

Product Description

tesa® 4308 is a slightly crêped paper masking tape which has been developed especially for high demanding masking applications in the automotive refinish and transportation industry.

tesa® 4308 withstands temperatures up to 100°C. It can be used either with 2 component or water based paints. The backing avoids penetration of lacquer or paint.

tesa® 4308 can be removed easily without any residues and leaving sharp paint edges.

Sustainable Aspects



For more information: <https://www.tesa.com/product-sustainability>

Application Fields

- Ambitious lacquering work
- Clean paint edges
- Protection of delicate surfaces

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- | | | | |
|--------------------|-----------------------|--|--------|
| • Backing material | slightly-creped paper | • Total sustainable product excl. liners by weight (acc. EN 16785) | 50 % |
| • Type of adhesive | natural rubber | • Total thickness | 170 µm |

Properties/Performance Values

- | | | | |
|-----------------------|---------|-----------------------------------|-----------|
| • Elongation at break | 13 % | • Hand tearability | very good |
| • Tensile strength | 53 N/cm | • Paint anchorage | very good |
| • Conformability | good | • Sharp colour edge | very good |
| • Easy to remove | yes | • Temperature resistance (60 min) | 100 °C |

Adhesion to Values

- | | |
|---------|--------|
| • steel | 4 N/cm |
|---------|--------|

For latest information on this product please visit <http://l.tesa.com/?ip=04308>



tesa® 4308

Product Information

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

For latest information on this product please visit <http://l.tesa.com/?ip=04308>