




Example image

APPLICATION PURPOSES

- For cold and hot potable water
- For cooling and heating water without antifreeze agent
- For service water and process water
- For treated water
- For rainwater with a pH value ≥ 5.5
- For grey and black water with a pH value ≥ 5.5
- For extinguishing water (wet)
- For extinguishing water (wet/dry, dry)
- For sprinklers (wet)

- For chemicals and technical liquids
- For compressed air (oil purity class 0–3)
- For negative pressure
- For inert gases (e.g. nitrogen)
- For industrial gases (e.g. acetylene, shielding gases)
- For technical building systems, industry and shipbuilding

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed

- Union nut made of brass
- Seal ring made of CIIR, black
- Flat gasket made of EPDM
- Pressing socket with transparent protection plug

TECHNICAL DATA

Medium temperature with flat gasket EPDM	0–100 °C
Product material	CrNiMo steel 1.4401 (EN 10088)

Art. no.	DN	d, ø mm	G "	L cm	Z cm
35320	12	15	3/4	6.6	2.6
35321	15	18	3/4	6.9	2.9
35322	20	22	1	7.2	3

Art. no.	DN	d, ø mm	G "	L cm	z cm
35323	25	28	1 1/4	7.7	3.1
35324	32	35	1 1/2	8.6	3
35325	40	42	1 3/4	9.5	3.5
35326	50	54	2 3/8	11.3	4.3