

HG 2320 E



HG 2320 E

Digitally controlled precision.

Technical Specifications

- Dimensions (LxWxH): 253 x 86.5 x 200 mm
Power supply: 230 V, 50/60 Hz
Output: 2300 W
Temperature: 80 - 650 °C, infinitely variable
Airflow rate: 150 - 500 l/min, infinitely variable
Stages: 2
Highlights: Safety heat indicator, 4 memory programmes, LOC function, 1-hand operation, easy-to-change power cord, soft grip, hanger, better weight balance
HL Scan and fine dust filter
- New accessories:
Power cord length: 3 m
Motor: brush motor
Heating element: ceramic heating element
Motor life: 1,000 h
- Package weight: gross: 1220 g; net: 1025 g
Package dimensions: 257 x 88 x 234 mm
Customs tariff number: 84198998
Country of origin: Romania
Region of origin: 03
Paper & board weight: 132 g
Plastics weight: 0 g

