



5W USB Adapter with Interchangeable Plugs PSB05R Series Meets Level V and Ecodesign Requirements



Features

- USB Socket
- Field Changeable AC Plugs
- Ecodesign ErP Directive 2009/125/EC level 2 annex 1b Compliant
- Low Leakage Current
- UL 94 V0 Flammability
- No Load Power Consumption < 0.3 Watt
- CEC Level V Compliance

Applications

- Wireless Communications
- Portable Equipment
- Peripherals
- Networking

Safety Approvals

- cUL/UL
- CE
- TUV
- C-Tick
- SAA

Mechanical Characteristics

- Length: 71.7mm (2.82in)
- Height: 29.79 (1.17in)
- Width: 45mm (1.77in)
- Weight: 128 (4.5oz)

Output Specifications

Model	DC Output Voltage	Load		Ripple ⁽¹⁾ P-P (max.)	Regulation Line & Load	Efficiency Level
		Min.	Max.			
PSB05R-050Q(A)-R	5V	0A	1A	55mV	±5%	V

(1) Measured by using a 12-inch twisted pair terminal with a 10uF EC capacitor and a 0.1uF ceramic in parallel, measured at maximum load.

PhiHong is not responsible for any error, and reserves the right to make changes without notice. Please visit our website at www.phihong.com for the most up-to-date specifications and contact information.