

## Flanging tool, metric die 6 mm - 14 mm



### Description:

- Capacity: pipes diam. 6 to 14 mm.
- Allows to produce flanges tapered at 45°, at the end of copper pipes without annealing the metal.
- BP.115 dimensions: 332 x 143 x 67 mm.
- 239.MU: Inch dies: pipes Ø from 3/16" to 5/8".

	Length L [mm]	Height H [mm]	Length [mm]	Weight [Kg]
239	332.0	67.0	143.0	1.52