

## FEATURES

- Complete with 2 metres of cable
- Sealed to IP40
- Single pedal foot operated switches
- Durable and reliable with steel housing for long life

## RS PRO General Purpose Momentary Metal Foot Switch - Mild Steel Case Material, SP- CO, 3 A Contact Current, 250V Contact

RS Stock No.: 251-2230



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

RS PRO single pole versatile foot switch with a durable steel housing for long life and high reliability. The foot switches have a low profile that helps eliminate operator fatigue, with only a small amount of pressure required to operate.

This range of foot pedal switches includes:

[254-2348](#) - Black robust metal foot switch, Momentary

[251-2230](#) - Black/White, Momentary

## General Specifications

<b>Contact Configuration</b>	SP-CO
<b>Switch Operation</b>	Momentary
<b>Case Material</b>	Mild Steel
<b>Switch Environment</b>	General Purpose
<b>Contact Material</b>	Silver
<b>Guard Cover</b>	No
<b>Standards Met</b>	2014/35/EU, EN 60950
<b>Colour</b>	Black, Grey
<b>Applications</b>	Foot switches are commonly used in applications where hands-free control is more practical or safer. They can be found on: Industrial machinery and smaller power tools, Hospital beds, Dentist Chairs, Lamps

## Electrical Specifications

<b>Contact Voltage Rating (AC)</b>	250V
<b>Contact Voltage Rating (DC)</b>	24V
<b>Contact Current Rating</b>	3A

## Mechanical Specifications

Length	90mm
Height	66mm
Dimensions	90mm x 66mm x24mm
Width	24mm

## Operation Environment Specifications

Operating Temperature	-5°C to 40°C
-----------------------	--------------

## Protection Category

IP Rating	IPX2
-----------	------

## Approvals

Compliance/Certifications	RoHS Certificate Of Compliance
---------------------------	--------------------------------





