



### Main

Range	Resi9
Product or component type	Enclosure
Enclosure type	Versatile enclosure
Nb of 18 mm modules per row	18
Provided equipment	3 x grid
Type of door	Without
Standards	IEC 60670-1
Colour	Enclosure: white (RAL 9003)

### Complementary

Enclosure mounting	Surface
Nb of horizontal rows	3
Mounting plate description	Perforated
Enclosure material	Self-extinguishing material
Net weight	2260 g
Width	357 mm
Height	500 mm
Depth	108 mm
Internal depth	106 mm

### Environment

Fire resistance	750 °C conforming to EN/IEC 60695-2-11
IP degree of protection	IP40 with closed door conforming to EN/IEC 60529
IK degree of protection	IK08
Ambient air temperature for operation	-15...60 °C

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>