



DWE560K

65MM COMPACT CIRCULAR SAW IN KITBOX

Features and Benefits

- Compact, Lightweight, Easy to use circular saw with 65mm depth of cut
- High power 1350W motor gives increased cutting performance
- Cutaway inner guard gives improved line of sight to cutting line
- Dust blower clears dust and debris from cut line
- Efficient dust extraction port to minimise airborne dust particles when connected to a dust extraction unit
- Direct compatibility with DEWALT AirLock system for easy, secure connection to extraction hose

Standard Equipment

- 24 tooth saw blade
- Dust Extraction Spout
- Rip Fence
- Blade Spanner
- Heavy Duty Carry Case

Specifications	
Power Input	1350 Watts
Power Output	850 Watt
No Load Speed	5500 rpm
Blade Diameter	184 mm
Blade Bore	16 mm
Bevel Capacity	48 °
Max. Depth of Cut at 90°	65 mm
Max. Depth of Cut at 45°	42 mm