



ENGLISH

Datasheet

RS Site Light A-Frame Stand, Fluorescent Tube T8, 18 W, 110 V IP55 Stock Number - 670-2730



Description

This range of 110V fluorescent plasterers lights provide many uses around the workplace and are supplied with foldaway stands for ease of storage and transportation.

Features

- High frequency control gear with flicker-free quick start
- Power factor corrected
- Supplied with 16A plug and 2 x 16A sockets on frame
- Polycarbonate base and diffuser
- Adjustable stand on 5' versions
- Fixed stand on 2' versions
- 3 hour emergency duration
- 1 year guarantee

Range

110V 5' 58W single plasterers light	BBIPL158W
110V 5' 58W single plasterers light, Emergency	BBIPL158WEM
110V 2' 18W twin plasterers light	BBIPL218W
110V 2' 18W twin plasterers light on A-frame stand	BBIL218W

**Technical Specification**

Voltage	110V ~ 50Hz
Ballast	Integral high frequency
Lamp	2' 18W T8 (not included) 5' 58W T8 (not included)
EM Battery	6V 4.0Ah Ni-Cd
IP Rating	IP65
Plug	16A (BS EN 60309)
Sockets	2 x 16A (BS EN 60309)
Cable Length	5m (3m on BBIL218W)

Height (mm)

	Height
BBIPL158W	1600mm
BBIPL158WEM	1600mm
BBIPL218W	1600mm
BBIL218W	900mm

Standards

- EN 60598-1
- BS EN 60598-2-7
- BS EN 60309