

## Han 48M Surf. mount. 2xM40 1Lever Cover



Image is for illustration purposes only. Please refer to product description.

Part number	19 37 048 0298
Specification	Han 48M Surf. mount. 2xM40 1Lever Cover
HARTING eCatalogue	<a href="https://harting.com/19370480298">https://harting.com/19370480298</a>

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han <sup>®</sup> M
Type of hood/housing	Surface mounted housing
Description of hood/housing	With metal cover
Type	High construction

### Version

Size	48 B
Version	Side entry
Number of cable entries	2
Cable entry	2x M40
Locking type	Single locking lever
Field of application	Hoods/housings for rough environments
Pack contents	Blind way for one cable entry

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12



**Pushing Performance**  
Since 1945

## Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	FPM
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

## Commercial data

Packaging size	1
Net weight	1,349 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140171404
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466