










GENERAL TOLERANCES (UNLESS SPECIFIED)	
10 ^{UNDER}	±0.2
10 ^{OVER} 30 ^{UNDER}	±0.25
30 ^{OVER}	±0.3
ANGULAR±3°	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex							
mm		20:1													
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 739518 DRWN: TNAKAGAWA01 2023/02/21 CHK'D: SMARUYAMA 2023/06/02 APPR: YNAITO 2023/06/02				0.5 MM PITCH B-TO-B CONN. HEIGHT = 3 PLUG							
								ANGULAR TOL ± 30°		PRODUCT CUSTOMER DRAWING					
								4 PLACES ± 0.2							
								3 PLACES ± 0.25							
2 PLACES ± 0.3		DOCUMENT NUMBER SD-53748-002		DOC TYPE PSD	DOC PART 001	REVISION F									
1 PLACE ±															
0 PLACES ±															
INITIAL REVISION: DRWN: NAKAMURAA 2008/12/08 APPR: NUKITA 2009/01/09															
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						A3-SIZE		53748		SEE SHEET 1		GENERAL		2 OF 2	



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
GENERAL TOLERANCES (UNLESS SPECIFIED) 10_{UNDER} 10_{OVER}30_{UNDER} 30_{OVER} ANGULAR±3° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 739518 DRWN: TNAKAGAWA01 CHK'D: SMARUYAMA APPR: YNAITO 2023/02/21 2023/06/02 2023/06/02 INITIAL REVISION: DRWN: NAKAMURAA APPR: NUKITA 2008/12/08 2009/01/09 THIRD ANGLE PROJECTION  DRAWING A3-SIZE SERIES 53748		molex 0.5 MM PITCH B-TO-B CONN. HEIGHT = 3 PLUG EMBOSS TAPE PACKAGE PRODUCT CUSTOMER DRAWING DOCUMENT NUMBER SD-53748-005 MATERIAL NUMBER SEE SHEET 2-5 DOC TYPE PSD DOC PART 001 REVISION F CUSTOMER GENERAL SHEET NUMBER 1 OF 5			
		mm		NTS							
		GENERAL TOLERANCES (UNLESS SPECIFIED)									
		ANGULAR TOL ± 30°									
		4 PLACES ± 0.2									
3 PLACES ± 0.25											
2 PLACES ± 0.3											
1 PLACE ±											
0 PLACES ±											

引き出し方向
PULL OUT DIRECTION




16mm 幅キャリアテープ
16mm WIDTH CARRIER TAPE

16	17.5	10.1	9.1	3.7	53748-0208	20
キャリアテープ幅 CARRIER TAPE WIDTH		D	(C)	(B)	(A)	MATERIAL NO. 極数 CKT.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex		
mm		NTS							
GENERAL TOLERANCES (UNLESS SPECIFIED)		GENERAL TOLERANCES (UNLESS SPECIFIED)		0.5 MM PITCH B-TO-B CONN. HEIGHT = 3 PLUG EMBOSS TAPE PACKAGE					
		ANGULAR TOL ± 30 °							
GENERAL TOLERANCES (UNLESS SPECIFIED)		4 PLACES ± 0.2		EC NO: 739518 DRWN: TNAKAGAWA01 CHK'D: SMARUYAMA APPR: YNAITO 2023/02/21 2023/06/02 2023/06/02					
		3 PLACES ± 0.25							
10 _{UNDER}		±0.2		PRODUCT CUSTOMER DRAWING					
10 _{OVER} 30 _{UNDER}		±0.25							
30 _{OVER}		±0.3		DOCUMENT NUMBER SD-53748-005 DOC TYPE PSD DOC PART 001 REVISION F					
ANGULAR±3°		1 PLACE ±							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		0 PLACES ±		THIRD ANGLE PROJECTION DRAWING A3-SIZE SERIES 53748					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING		MATERIAL NUMBER SEE TABLE CUSTOMER GENERAL SHEET NUMBER 2 OF 5					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SERIES							

DOCUMENT STATUS	P1	RELEASE DATE	2023/06/02	09:12:01
-----------------	----	--------------	------------	----------




24mm 幅キャリアテープ
24mm WIDTH CARRIER TAPE

24	25.5	15.1	14.1	7.4	53748-0408	40
		12.6	11.6	4.9	53748-0308	30
キャリアテープ幅 CARRIER TAPE WIDTH	D	(C)	(B)	(A)	MATERIAL NO.	極数 CKT.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:		molex		
DIMENSION UNITS mm		SCALE NTS		0.5 MM PITCH B-TO-B CONN. HEIGHT = 3 PLUG EMBOSS TAPE PACKAGE		
GENERAL TOLERANCES (UNLESS SPECIFIED)		ANGULAR TOL ± 3.0 °		PRODUCT CUSTOMER DRAWING		
10 ^{UNDER} ±0.2		4 PLACES ± 0.2		EC NO: 739518 DRWN: TNAKAGAWA01 CHK'D: SMARUYAMA APPR: YNAITO		
10 ^{OVER} 30 ^{UNDER} ±0.25		3 PLACES ± 0.25		INITIAL REVISION:		
30 ^{OVER} ±0.3		2 PLACES ± 0.3		DRWN: NAKAMURAA APPR: NUKITA		
ANGULAR+3°		1 PLACE ±		DOCUMENT NUMBER		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		0 PLACES ±		SD-53748-005		
THIRD ANGLE PROJECTION		DRAWING		PSD		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SERIES		001		
A3-SIZE		53748		F		
MATERIAL NUMBER		CUSTOMER		SHEET NUMBER		
SEE TABLE		GENERAL		3 OF 5		



引き出し方向
PULL OUT DIRECTION

トップテープ
TOP TAPE



SECT:Y-Y

44mm 幅キャリアテープ
44mm WIDTH CARRIER TAPE



SECT:X-X
(SCALE:4-1)

44	45.5	25.1	24.1	18.7	53748-0808	80
		22.6	21.6	16.2	53748-0708	70
キャリアテープ幅 CARRIER TAPE WIDTH	D	(C)	(B)	(A)	MATERIAL NO.	極数 CKT.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:		molex		
DIMENSION UNITS mm	SCALE NTS	GENERAL TOLERANCES (UNLESS SPECIFIED)				
GENERAL TOLERANCES (UNLESS SPECIFIED)				0.5 MM PITCH B-TO-B CONN. HEIGHT = 3 PLUG EMBOSS TAPE PACKAGE		
ANGULAR TOL ± 3.0 °						
4 PLACES ± 0.2		EC NO: 739518		PRODUCT CUSTOMER DRAWING		
3 PLACES ± 0.25		DRWN: TNAKAGAWA01				
2 PLACES ± 0.3		CHK'D: SMARUYAMA		DOCUMENT NUMBER		
1 PLACE ±		APPR: YNAITO				
0 PLACES ±		INITIAL REVISION:		SD-53748-005	PSD	
ANGULAR+3°		DRWN: NAKAMURAA				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		APPR: NUKITA		REVISION		
THIRD ANGLE PROJECTION		DRAWING		MATERIAL NUMBER	CUSTOMER	
		A3-SIZE				
		SERIES		SHEET NUMBER		
		53748		5 OF 5		