


| Art.-No.  | VE | PG  | EAN   |
|-----------|----|-----|---|
| 234202016 | 1  | 132 | <br>4 008224 6 18991 |

DUOversal Plus, 6=12, all sockets with connection option for one grounding-type plug or two euro-plugs, with illuminated switch (2-pole), with shutter, with 35° turned sockets, 52mm distance between sockets, cable H05VV-F3G1,5mm<sup>2</sup>, 3m, mountable, 16A, 250V~, white



| Technical data                                   |                    | 234202016 |
|--|--------------------|-----------|
| Housing shape                                    | Rectangular        |           |
| Material   | Plastic            |           |
| Material quality                                 | Thermoplastic      |           |
| Surface protection                               | Untreated          |           |
| Surface finishing                                | Matt               |           |
| Colour   | White              |           |
| Degree of protection (IP)                        | IP20               |           |
| Angle rotated central insert                     | 35°                |           |
| Number of socket outlets with protective contact | 6                  |           |
| Number of Euro socket outlets                    | 12                 |           |
| Number of CEE socket outlets                     | 0                  |           |
| Number of socket outlets with earth pin          | 0                  |           |
| Number of cold device socket outlets             | 0                  |           |
| Residual current circuit breaker (RCCB)          | No                 |           |
| Mains filter                                     | No                 |           |
| Number of other socket outlets                   | 0                  |           |
| Over voltage protection                          | No                 |           |
| Nominal current                                  | 16A                |           |
| Core cross section                               | 1.5mm <sup>2</sup> |           |
| With cover                                       | No                 |           |
| Transparent                                      | No                 |           |
| Length of power cord                             | 3m                 |           |
| Rotated central insert                           | Yes                |           |