

PREVOST FILTRATION - SINGLE UNITS

Progressive pressurization valve



Part number	Female thread	Flow rate at 6.00 bar (l/min) ($\Delta P = 1.00$ bar)	Max. operating pressure (bar)	Net weight (Kg)
ATU S100	G1/8	1400.00	10.00	0,242
ATU S101	G1/4	2500.00	10.00	0,242
ATU S102	G3/8	5300.00	10.00	0,55
ATU S103	G1/2	6400.00	10.00	0,55

