

SAC-17P-MS/10,0-PUR/FS SCO - Sensor/actuator cable



1402497

<https://www.phoenixcontact.com/in/products/1402497>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 17-position, PUR halogen-free, black RAL 9005, Plug straight M12 SPEEDCON, coding: A, on Socket straight M12 SPEEDCON, coding: A, cable length: 10 m

Commercial data

Item number	1402497
Packing unit	1 pc
Minimum order quantity	25 pc
Product key	AF1CGA
GTIN	4046356620024
Weight per piece (including packing)	748 g
Weight per piece (excluding packing)	748 g
Country of origin	DE

SAC-17P-MS/10,0-PUR/FS SCO - Sensor/actuator cable



1402497

<https://www.phoenixcontact.com/in/products/1402497>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	17
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	V0
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	PA 6.6
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	30 V AC
	30 V DC
Nominal current I_N	1.5 A

Signaling

Status display	no
Status display present	No

Connector

Connection 1

Type	Plug straight M12 SPEEDCON
Number of positions	17
Locking type	SPEEDCON
Coding type	A

Connection 2

Type	Socket straight M12 SPEEDCON
Number of positions	17
Locking type	SPEEDCON
Coding type	A

SAC-17P-MS/10,0-PUR/FS SCO - Sensor/actuator cable



1402497

<https://www.phoenixcontact.com/in/products/1402497>

Cable/line

Cable length	10 m
PUR halogen-free black [PUR]	
Dimensional drawing	
Number of positions	17
Shielded	no
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	18x 0.10 mm
AWG signal line	26
Conductor cross section	17x 0.14 mm ² (Signal line)
Wire diameter incl. insulation	1 mm ±0.05 mm (Signal line)
External cable diameter	7.80 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	black RAL 9005
Conductor material	Tin-plated Cu litz wires
Material wire insulation	PP
Single wire, color	white, brown, green, yellow, gray, pink, blue, red, black, violet, gray-pink, red-blue, white-green, brown-green, white-yellow, yellow-brown, white-gray
Overall twist	17 wires twisted in layers
Max. conductor resistance	142 Ω/km
Smallest bending radius, fixed installation	78 mm
Smallest bending radius, movable installation	39 mm
Dynamic load capacity (bending)	Max. bending cycles: 4000000, Bending radius: 60 mm, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s ²
Resistance to oil	DIN VDE 0472 Part 803, test type B
Other resistance	Hydrolysis and microbe resistant as per VDE 0282 section 10 partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)
Special properties	Low adhesion surface
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

IP65

SAC-17P-MS/10,0-PUR/FS SCO - Sensor/actuator cable



1402497

<https://www.phoenixcontact.com/in/products/1402497>


Degree of protection	IP67
	IP68
Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)
	-40 °C ... 80 °C (cable, fixed installation)
	-20 °C ... 80 °C (Cable, flexible installation)

1402497

<https://www.phoenixcontact.com/in/products/1402497>


Drawings

Schematic diagram



Pin assignment M12 male connector, 17-pos., male side view

Schematic diagram




Pin assignment M12, 17-pos., socket side view

SAC-17P-MS/10,0-PUR/FS SCO - Sensor/actuator cable

1402497


<https://www.phoenixcontact.com/in/products/1402497>

Dimensional drawing



Socket M12-SPEEDCON, straight, shielded

Dimensional drawing



M12 SPEEDCON plug, straight, shielded

SAC-17P-MS/10,0-PUR/FS SCO - Sensor/actuator cable



1402497

<https://www.phoenixcontact.com/in/products/1402497>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1402497>

	UL Listed Approval ID: E221474			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	30 V	1 A	-	-

SAC-17P-MS/10,0-PUR/FS SCO - Sensor/actuator cable



1402497

<https://www.phoenixcontact.com/in/products/1402497>

Classifications

ECLASS

ECLASS-11.0	27060311
ECLASS-12.0	27060311
ECLASS-13.0	27060311

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-17P-MS/10,0-PUR/FS SCO - Sensor/actuator cable



1402497

<https://www.phoenixcontact.com/in/products/1402497>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in