





1. RECEPTACLE ACCEPTS A .008-.014 THICK I.C. LEAD.
2. TWO .000030 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON SOLDER LEGS, BALANCE OF CONTACT NICKEL PLATED.
3. TWO .000015 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON SOLDER LEGS, BALANCE OF CONTACT NICKEL PLATED.
4. TUBE LOADED.



SECTION A-A
SCALE 10:1



RECOMMENDED MOUNTING HOLE PATTERN

| | | | | |
|--------------------------|--------|--------------------|--|------------|
| OBSOLETE | TINNED | PHOS.BRZ. .006 THK | GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK | 2-382189-5 |
| SUPERSEDED BY 2-382189-2 | 2 | PHOS.BRZ. | GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK | 2-382189-4 |
| OBSOLETE | TINNED | PHOS.BRZ. | GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK | 2-382189-3 |
| | 3 | BE.CU. | GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK | 2-382189-2 |
| | TINNED | BE.CU. | GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK | 2-382189-1 |
| CONTACT FINISH | | CONTACT MAT'L | HOUSING MATERIAL | PART NO. |

THIS DRAWING IS A CONTROLLED DOCUMENT.

| | | |
|------------------|--|--------------|
| DW | R BROWN | 17NOV00 |
| OK | H WYNKOOP | 17NOV00 |
| APVD | H WYNKOOP | 17NOV00 |
| NAME | SOCKET ASSY, DIP, OTC, RET LEG, 32 POS, DIPLOMATE DL | |
| PRODUCT SPEC | 108-1066 | |
| APPLICATION SPEC | 114-1049 | |
| SIZE | A1 | 00779 |
| CAGE CODE | 382189 | |
| DRAWING NO | 382189 | |
| RESTRICTED TO | - | |
| MATERIAL | SEE TABLE | FINISH |
| WEIGHT | - | SCALE |
| CUSTOMER DRAWING | SCALE 5:1 | SHEET 1 OF 1 |