



ENGLISH

Datasheet

**RS Pro Acrylic Tube, 1000mm x 22mm OD x 16mm ID**

RS Stock No: **408-4024**



## Product Details

RS Pro acrylic tube measures 1000 mm long with a inner and outer diameter of 16 x 22 mm respectively. This extruded thermoplastic acrylic tubes has an excellent optical properties and offers good resistance to most inorganic chemicals, oils, dilute acids/alkalis and weathering. The tube is tested for M 90 Rockwell hardness.

## Features and Benefits

- Extruded thermoplastic acrylic tubes with excellent optical properties
- Measures 1000 mm x 22 mm OD x 16 mm ID
- Good resistance to most inorganic chemicals, oils, dilute acids/alkalis and weathering

**Specifications:**

Colour	Clear
Hardness	M 90 Rockwell
Material	Acrylic
Tube Form	Round
Density	1.18 g/cm <sup>3</sup>
Elongation	5%
Inner Diameter	16 mm
Length	1000 mm
Maximum Operating Temperature	+70°C
Outer Diameter	22 mm
Water Absorption	0%
Tensile Strength	60 MPa