



Accessories: Connectors BKS-S 20-4-PU-

Common Data

Version	Connector, right angle, 3 pin, 2 LED
PU-Cable	
Usable with	on Sensors with connection S4 (DC,
PNP, n.o., M12)	
Manufacturer	Lumberg
Ambient temperature	-25°C...+90°C
Function display	yes
Supply voltage display	yes

Mechanical Data

Measurements WxHxD or Dia x D	27x31x14mm
Material	Housing Polyether TPU
Protection class per IEC 60529	68 acc. BWN Pr.20IP
Cable version	fully potted, LifY-Y-11Y-0
Conductor cross section	3 x 0,34mm ² mm ²

Electrical Data

Supply voltage	10...30VDCV
----------------	-------------



Datasheet number::

Definitions see general catalog.
If not otherwise noted, ratings according to
IEC 60947-5-2 (DIN EN60947-5-2)

Balluff GmbH
P.O.Box 1160
73761 Neuhausen Germany
Phone (07158) 173-0 Fax (07158) 5010