



Get great photos, documents and web pages, plus the versatility of being able to copy and scan too, from one affordable device. Print beautiful photos without a PC, make quick colour copies and scan paperwork into your PC. Do all this – and more.

The HP Photosmart C4480 All-in-One Printer, Scanner, Copier is designed for people who want to be able to print everything from documents and web pages to photos – and will value the ability to scan and copy from the same compact device.

Print, scan and copy paperwork, photos and more with one versatile machine.

Don't limit yourself to printing – enjoy the convenience of being able to scan and copy too with this compact all-in-one. Choosing versatility doesn't mean compromising on quality either. Print laser-quality documents and lab-quality photos using HP Vivera inks – you can even choose optional 6-ink colour¹ for professional-quality photos. Get fast copies too with speeds of up to 30 ppm black, 23 ppm colour. Use the scanner to digitise photos or documents for sharing or safe-keeping.

Get great value with this affordable all-in-one and a choice of ink cartridges.

Enjoy the best of both worlds with an all-in-one that's not only affordably priced but also highly efficient to use. For a start, HP ink cartridges are designed for efficient usage so they save you ink and money. You can also choose the replacement cartridges that best suit your needs, with high-capacity cartridges¹ giving you 3x more prints² and the convenience of fewer cartridge changes. And with an Energy Star-qualified product, you'll keep control of your running costs too.

See how much you can do with easy-to-use HP technologies.

Everything about this HP all-in-one is designed to help you get the job done, more easily. Want to print photos without switching on your PC? Just pop in your memory card and choose which ones to print via the 3.8 cm display. Print a lot of web pages? HP Smart Web Printing adjusts web pages so they fit on the paper. There's an automatic paper sensor that optimises your settings, and there's even software that will help you edit, print and share your photos. It really couldn't be easier.

¹ Not included, sold separately

² Compared to HP 350 Black Ink Cartridge and HP 351 Tri-colour Ink Cartridge.

Technical specifications

Print				
Print technology	HP Thermal Inkjet			
Display	C4480: 3.8 cm LCD (colour graphics)			
Ink Types	Dye-based (colour), pigment-based (black)			
Print speed	Document type	Draft	Normal	Best
	Black text A4:	Up to 30 ppm	Up to 8.9 ppm	
	Mixed text/colour graphics A4:	Up to 23 ppm	Up to 5.3 ppm	
	10 x 15 cm colour photo (photo paper):	As fast as 25 sec	As fast as 49 sec	
	Dependent upon type, print mode and approximate figures. Exact speed will vary depending on the system configuration, software program and document complexity.			
Print quality	Black: Up to 1200 rendered dpi black when printing from a computer, Colour: Up to 4800 x 1200 optimised dpi colour when printing from a computer and 1200 input dpi			
Borderless printing	Yes (up to panorama, A4 and more)			
Printer languages	HP PCL 3 GUI			
Scan	Resolution: Optical: Up to 1200 dpi; Hardware: Up to 1200 x 2400 dpi; Enhanced: Up to 19200 dpi			
	Maximum document size: 215 x 297 mm			
	Scan speed: 10 x 15 cm colour photo into Microsoft® Word: less than 48 sec; OCR a full page of text into Microsoft® Word: less than 22 sec; preview: less than 13 sec (Scan speeds vary according to complexity of the document)			
	Type: Flatbed; Bit depth: 48-bit; Twain version: Mac: Version 1.8; Windows®: Version 1.9; Scan technology: CIS; Greyscale: 256			
Copy				
Copy speed	Document type	Draft	Normal	Best
	Black text A4:	Up to 30 cpm	Up to 7.7 cpm	Up to 0.7 cpm
	Mixed Text/Colour graphics A4:	Up to 23 cpm	Up to 7.7 cpm	Up to 0.7 cpm
	Resolution: Black: Up to 600 dpi; Multiple copies: Up to 50; Reduce/Enlarge: 50 to 400%			
Duty cycle	Up to 1000 pages pages per month			
ADF capacity	None			
Media types	Paper (plain, inkjet, photo), envelopes, transparencies, labels, cards, HP premium media, iron-on transfers			
Automatic paper type sensor	Yes			
Media sizes	Standard: A4 (210 x 297 mm), A5 (148 x 210 mm), B5 (176 x 250 mm), DL (110 x 220 mm), C6 (114 x 162 mm), A6 (105 x 148 mm), 300 x 100 mm, 130 x 180 mm, 100 x 150 mm, custom: 77 x 127 to 215 x 610 mm			
Max. media weight range	A4: 70 to 90 g/m², HP envelopes: 70 to 90 g/m², HP cards: up to 200 g/m², HP photo paper: up to 280 g/m²			
Paper handling	Standard: 100-sheet input tray			
Media handling/input	Sheets: Up to 100, envelopes: Up to 10, cards: Up to 20, transparencies: Up to 20, 10 x 15 cm photo: Up to 20			
Duplex printing	None (not supported)			
Power	Requirements: Input voltage 100 to 240 VAC (+/- 10%), 50/60 Hz (+/- 3 Hz), supply: External			
Power consumption	Maximum: 70 watts maximum (active/printing), 7.5 watts maximum (ready)			
Interface and connectivity	C4480: USB - compatible with USB 2.0 specifications, memory card slots			
Memory	Slots: 4 slots: Memory Stick®, Memory Stick® Duo, Secure Digital/MultiMediaCard, Secure Digital High Capacity Card, xD-Picture Card; Standard: 32 MB; Maximum: 32 MB			
Software included	HP Photosmart Essential 2.5, HP Smart Web Printing 2.0, OCR Software			
Dimensions (w x d x h)	Out of package: C4480: 434 x 290 x 162 mm, , packaged: C4480: 470 x 196 x 334 mm			
Weight	Out of package: C4480: 5.06 kg, packaged: C4480: 6.48 kg			
Country of origin	Product of Malaysia			
Operating systems compatibility	Mac OS X v10.3.9, v10.4, v10.5; Windows Vista® (32 and 64-bit); Microsoft® Windows® XP Home and Professional (32 and 64-bit)			
Energy Star	Yes			
Supplies life	For information on page yield, visit www.hp.com/go/learnaboutequipment , or see product packaging			
Warranty	Standard one-year limited hardware warranty. Warranty and support options vary by product, country and local legal requirements.			

Ordering information

Q8388B	HP Photosmart C4480 All-in-One Printer, Scanner, Copier, HP 350 Black Ink Cartridge, HP 351 Tri-colour Ink Cartridge, HP Photosmart Essential software, setup guide, reference guide, power supply, power cord
Accessories	
C6520A	HP USB Cable, 3m
Supplies	
CB335EE	HP 350 Black Inkjet Print Cartridge with Vivera Ink
CB337EE	HP 351 Tri-colour Inkjet Print Cartridge with Vivera Inks
CB336EE	HP 350XL Black Inkjet Print Cartridge with Vivera Ink
CB338EE	HP 351XL Tri-colour Inkjet Print Cartridge with Vivera Inks
C9369EE	HP 348 Photo Inkjet Print Cartridge with Vivera Inks
Media	
Q8691A	HP Advanced Glossy Photo Paper 250 g/m²-10 x 15 cm borderless/25 sht
Q5456A	HP Advanced Glossy Photo Paper 250 g/m²-A4/210 x 297 mm/25 sht
CHP710	HP All-In-One Printing Paper 80 g/m²-A4/210 x 297 mm/500 sht
Service & Support	
UG062E	HP Care Pack, Next Business Day Exchange Service, 3 years
UG187E	HP Care Pack, Exchange Service (standard turn around time), 3 years
UG235E	HP Care Pack, Return to Depot Hardware Support Service, 3 years.
(UG235E: Only Baltics, Greece, Poland, Turkey, EEM, Slovenia, Czech Republic, Slovakia, Hungary. UG062E/UG187E: Rest of Europe).	
For a complete list of supplies, media and accessories, please refer to the HP website at http://www.hp.com	

<http://www.hp.com>

