

## Datasheet

# RS Pro New Zinc Plated Steel Nylon Insert Locking Nut, M20

RS Stock No: **122-4377**



## Product Details

RS Pro nylon insert locking nut made of new zinc plated steel offers corrosion resistance. This nut is self locking due to glass filled nylon insert and features M20 metric internal threading to couple with threaded rod. The nut is designed to remain secure despite conditions of severe vibration. Having a nylon insert makes the nut better at sealing the bolt thread against leaking water, oil and other liquids. The nut offers greater resistance to vibrations and torque and remains locking up to 250 deg C. This locking nut is highly resistant to organic acids, solvent, oil and mineral salt.

## Features and Benefits

- Greater resistance to vibrations and torque
- Mild steel grade 8.8
- Retains locking ability up to 250°C
- Resistant to organic acids, solvent, oil and mineral salt
- 360° seal
- Used by builders, DIY enthusiasts, joiners and Roofers

**Specifications:**

Finish	Zinc Plated
Material	Steel
Thread Size	M20
Type	Nylon Insert
Grade	8.8
Specification	DIN 985
Thickness	18.7 to 20 mm
Thread Pitch	2.5
Width Across Corners	32.95 mm
Width Across Flats	29.16 to 30 mm
Wrenching Height	14 mm