



Venue™ 11 Pro

The ultimate 2-in-1 flexibility: power of an Ultrabook, functionality of a desktop, portability of a tablet



A tablet for everyone

Whatever you are looking for in a tablet, we definitely have your type. With incredible features like a stunning Full HD screen with wide-angle viewing for watching video as well as advanced connectivity options to keep you in touch with the people and information that matters to you, the Dell Venue™ 11 Pro tablets are designed to tackle all your needs. Plus, all Dell Venue™ tablets are designed for easy integration with an array of accessories. With the new Dell Venue™ 11 Pro, you'll never have to settle again.

Connect, access, and share with ease

The Dell Venue™ 11 Pro comes equipped with a stunningly bright 10.8" Full HD IPS Display and wireless video technology¹ to make sharing and projecting a breeze. Be constantly connected to your data, your work, or favorite social media app with Dual-Band 2x2 Wi-Fi, Bluetooth 4.0, and mobile broadband² options. In addition, Dell Venue 11 Pro tablets come with Dell PocketCloud³ for accessing files on any remote device.

Amazing flexibility

Work and play the way that is most natural for you. The Dell Venue™ 11 Pro was engineered with extreme flexibility in mind with the ability to use USB 3.0 connections, Micro-SD storage devices, and a suite of accessories that allows the Dell Venue™ 11 Pro to be used as an Ultrabook or even a desktop supporting up to two displays.

Meaningful security and service

Protecting your personal information is no longer an option. The Dell Venue™ 11 Pro is ready for the challenge with hardware TPM and Dell Data Protection Security Tools available for every model.⁴

All Dell Venue™ 11 Pro tablets also come with a one year limited hardware warranty⁵.



Accessories that help you simply do more.

Convert your Dell Venue™ 11 Pro into a laptop with the Dell Tablet Mobile Keyboard or expand to a full desktop solution with the Dell Tablet Desktop Dock



Specifications

Feature	Technical specification
Display	10.8 inch IPS Display with FHD (1920 x 1080) resolution with 10-pt capacitive touch
Processor Options	Intel® Atom™ processor Z3770 (2MB Cache, up to 2.4GHz Quad-Core) Intel® Pentium™ 3560Y processor (2MB Cache, 1.2 GHz Dual -Core) Intel® Core™ i3 4020Y processor (3MB Cache, 1.5 GHz Dual -Core) Intel® Core™ i5 4210Y processor (3MB Cache, 1.5 GHz Dual -Core) Intel® Core™ i5 4300Y processor (3MB Cache, 1.6 GHz Dual -Core)
Hard Drive Options	32GB ⁷ , 64GB ⁷ , 128GB ⁷ , or 256GB ⁷ solid state storage
Memory	2GB DDR3 1333MHz Memory ⁸ 4GB or 8GB DDR3 1600MHz Memory ⁸
Graphics	Intel® Gen 7 Graphics or Intel® GT2 Graphics ⁸
Audio	Stereo Speakers with SRS premium audio and Adaptive noise cancellation Dual microphone.
Wireless LAN	Dell Wireless 1537 Dual-Band 2x2 802.11n WiFi Intel® 7260AC Dual-Band 2x2 802.11 ac WiFi (Intel® Core™ i5 vPro™ Configurations only) Near Field Communication (NFC)
Bluetooth	Bluetooth 4.0
Mobile Broadband ²	Dell Wireless 5570E (3G / HSPA+) or Dell Wireless 5808E (4G LTE/HSPA/EVDO) {US Only}
TPM	Hardware TPM
Battery	30Whr ⁹ or 37Whr ⁹ , Swappable battery (based on configuration)
Power Adapter	24 Watt AC Adapter
Webcam	Integrated 2MP HD Webcam (front) / 8MP (back)
Card Reader	Micro-SD Card Reader (SD, SDHC, SDXC, supporting up to 64GB)
Ports & Connectors	1 x Full size USB3.0. 1 x Headphone and microphone combo jack, 1 x micro HDMI
Weight	Starting at: 726g / 1.6lb ¹⁰
Dimensions	Starting at: Thickness 10.2mm - 15.4mm (based on model), Width: 177mm, Length: 280mm
Operating System	Windows 8.1
Warranty	1-Year Limited Hardware Warranty ⁵

Discover the entire line of Dell's amazing tablet family at Dell.com/tablets.

Important Information

¹ Requires a compatible Media Adapter and cable (sold separately) and an HDMI or composite AV-enabled display.

² Subject to service provider's broadband subscription and coverage area; additional charges apply.

³ Dell PocketCloud is available in US English Only. Not available in China.

⁴ Dell Data Protection \ Encryption Security Tools not available in all countries. Other Dell Data Protection \ Encryption available for purchase post launch.

⁵ For copy of Ltd Hardware Warranty, write Dell USA LP, Attn: Warranties, One Dell Way, Round Rock, TX 78682 or see www.dell.com/warranty. ⁷ Hard Drives: GB means 1 billion bytes and TB equals 1 trillion bytes; actual capacity varies with preloaded material and operating environment and will be less.

⁸ Memory: GB means 1 billion bytes and TB equals 1 trillion bytes; significant system memory may be used to support graphics, depending on other system memory sizes and other factors.

⁹ The stated Watt Hour (Whr) is not an indication of battery life.

¹⁰ Weights vary depending on configuration and manufacturing variability.

Offers vary by country; Features and specifications subject to change without notice. Availability and terms of Dell Services vary by region. Ask your service representative about available services in your area.

Copyright 2013 Dell Inc. All rights reserved. Venue is a trademark of Dell Inc. Intel, Atom, Ultrabook, and Core are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States of America and other countries. Microsoft, Windows, and Windows 8 are registered trademarks of Microsoft Corporation. Other trademarks or trade names may be used in this document to refer to either the entities claiming the marks and names or their products. Dell disclaims proprietary interest in the marks and names of others. Reproduction in any manner whatsoever without express written permission from Dell Inc. is strictly forbidden.

