

Technical sheet

TPZ800CV

Green flexible bollard H 800mm-d.80mm+plate-cylindrical head

Flexible shape memory green post, 80 mm diameter, cylindrical head, prevents damage to vehicles. In case of impact, the bollard deforms to return to its initial shape and without breaking the sealing or fixing. Resistant to tearing, pulling, and breaking. Used for separating and protecting different areas in the city and parking lots. Height 1000mm. To be fixed directly in the ground. Fixings not included. Multiple options available: chain ring, reflective tape, fixing, specific color.





Customs code	3926909790
EAN	3321360013118

Color : Green (RAL6005)

Material : Polyurethane

Specifications :

- Flexible memory-shaped bollard designed to prevent vehicle damage.
- In case of impact, the bollard deforms to its initial shape without breaking the anchoring or fixation.
- Resistant to tearing, pulling, and breaking.
- Various options available: head type, PMR standard, to be fixed or anchored, removable box, with or without reflective tape...

Height (mm)	Diameter (mm)	Dimensions plate (mm)	Type of post	Net weight (kg)
800	80	140x140	To fix	2,38

VISO
www.viso-cpn.com

VISO - 7 avenue Arago - ZI de la Vigne aux Loups - 91380 CHILLY-MAZARIN - France
Tél. + 33 (0)1 69 53 46 70 - Fax + 33 (0)1 69 53 46 80 - contact@viso-cpn.com / commande@viso-cpn.com