

MN series : To be used in compression only.

Optimum load is adjusted by changing hardness, in same shape.



Part No.	Optimum Load (kg/4 legs)	Resonance Point(Hz)	Resonance Magnification (dB)	Recommended Frequency(Hz)
MN-3	8~14	12~10	12	17~
MN-5	14~22	11~10	14~13	16~
MN-7	22~34	11~10	16~15	16~
MN-10	34~50	11~10	20~18	16~