

FEATURES

- **Sintered Bronze Material:** Provides high durability and resistance to wear, ensuring long service life.
- **Flanged Design:** Facilitates easy installation and alignment, reducing assembly time.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with varying loads, enhancing versatility.
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads, ensuring stability and reliability.
- **0.62 in Bore Size:** Compatible with a wide range of shafts, offering flexibility in use.
- **0.75 in Outside Diameter:** Standard sizing for easy integration into existing systems.

RS PRO 0.62 in Flanged Plain Bearing

RS Stock No: 528-226



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flanged plain bearing is designed for applications requiring reliable and efficient performance under varying load conditions. Made from sintered bronze, it offers excellent durability and resistance to wear, making it ideal for both static and dynamic applications.

General Specifications

Bore Size	0.62 in
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	0.75 in
Width	1-1/8 in

Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------

